



**HSG34T48PF, Heat Shrink Tubing,
0.750" ID Min.(Exp.), 0.375" ID
Max.(Rec.), #1 - 3/0, Polyolefin,
Thin Wall, Green, Shrink ratio-2:1, 4
Ft Reel.**

By Burndy
Catalog # [HSG34T48PF](#)



Heat Shrink Tubing, 0.750" ID Min.(Exp.), 0.375" ID Max.(Rec.),
#1 - 3/0, Polyolefin, Thin Wall, Green, Shrink ratio-2:1, 4 Ft Reel.

General

Color	Green
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810212820

Conductor Related

Conductor Range	#1 AWG to #3/0 AWG
Conductor Size	1AWG - 3/0AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T30OPF_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Video - Heat Shrink Product Overview & Installation](#)



A proud member of the Hubbell Family.