



HSG38FR250, Heat Shrink Tubing, 0.375" ID Min.(Exp.), 0.19" ID Max. (Rec.), #8 - #6, PVC, Fire retardant, Thin Wall, Green, 250 Ft Reel.



By Burndy
Catalog # [HSG38FR250](#)

Heat Shrink Tubing, 0.375" ID Min.(Exp.), 0.19" ID Max.(Rec.), #8 - #6, PVC, Fire retardant, Thin Wall, Green, 250 Ft Reel.

General

Catalog Number	HSG38FR250
Color	Green
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810266472

Conductor Related

Conductor Range	#8 AWG to #6 AWG
Conductor Size	6AWG - 4AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	40
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSG38FR250](#)