



HSG38T300PF, Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max. (Rec.), #8 - #6, Polyolefin, Thin Wall, Green, Shrink ratio-2:1, 25 Ft Reel.



By Burndy
Catalog # [HSG38T300PF](#)

Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max.(Rec.), #8 - #6, Polyolefin, Thin Wall, Green, Shrink ratio-2:1, 25 Ft Reel.

General

Catalog Number	HSG38T300PF
Color	Green
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810213704

Conductor Related

Conductor Range	#8 AWG to #6 AWG
Conductor Size	8AWG - 6AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSG38T300PF](#)