



HSM316T6PF18, Thin Wall Cross-Linked Polyolefin Heat Shrink Tubing, #12-18 AWG, 600 V, 6.00" L, Flame Retardant, Multiple Colors.

By Burndy
Catalog # HSM316T6PF18



Thin Wall Cross-Linked Polyolefin Heat Shrink Tubing, #12-18 AWG, 600 V, 6.00" L, Flame Retardant, Multiple Colors.

Application

For Terminations And Splices

General

Catalog Number	HSM316T6PF18
Color	Multiple Colors
Connector Type	THIN WALL TUBES
EU RoHS Indicator	Yes
Material	Cross-linked Polyolefin
Sub Brand	HEAT SHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
UPC	781810214619

Conductor Related

Conductor Range	#18 AWG to #12 AWG
Conductor Size	18AWG - 12AWG

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	180
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSM316T6PF18](#)
- [Video - Heat Shrink Product Overview & Installation](#)