



# HSR100FR100, Heat Shrink Tubing, 1.00" ID Min.(Exp.), 0.50" ID Max. (Rec.), 1/0 - 4/0, PVC, Fire retardant, Thin Wall, Red, 100 Ft Reel.



By Burndy  
Catalog # [HSR100FR100](#)

Heat Shrink Tubing, 1.00" ID Min.(Exp.), 0.50" ID Max.(Rec.), 1/0 - 4/0, PVC, Fire retardant, Thin Wall, Red, 100 Ft Reel.

## General

|                |                       |
|----------------|-----------------------|
| Catalog Number | HSR100FR100           |
| Color          | Red                   |
| Connector Type | THIN WALL TUBES/REELS |
| Material       | Polyvinyl chloride    |
| UPC            | 781810266618          |

## Conductor Related

|                 |                      |
|-----------------|----------------------|
| Conductor Range | #1/0 AWG to #4/0 AWG |
| Conductor Size  | 4/0AWG - 300kcmil    |

## Certifications And Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | Yes |
| Certification - ETL                | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | No  |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 2 |
|-----------------------|---|

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSC100FR\\_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSR100FR100](#)