



HSR12FR, Heat Shrink Tubing, 0.50" ID Min.(Exp.), 0.25" ID Max.(Rec.), #6 - #4, PVC, Fire retardant, Thin Wall, Red, 50 Ft Reel.



By Burndy
Catalog # [HSR12FR](#)

Heat Shrink Tubing, 0.50" ID Min.(Exp.), 0.25" ID Max.(Rec.), #6 - #4, PVC, Fire retardant, Thin Wall, Red, 50 Ft Reel.

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

General

| | |
|----------------|-----------------------|
| Catalog Number | HSR12FR |
| Color | Red |
| Connector Type | THIN WALL TUBES/REELS |
| Material | Polyvinyl chloride |
| UPC | 781810266649 |

Conductor Related

| | |
|-----------------|------------------|
| Conductor Range | #6 AWG to #4 AWG |
| Conductor Size | 4AWG - 1AWG |

Certifications And Compliance

| | |
|------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Standards - RoHS Compliance | CM |
| Status | |
| UL Listed | No |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 16 |
|-----------------------|----|

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSR12FR](#)