



HSR12T300PF, Heat Shrink Tubing, 0.50" ID Min.(Exp.), 0.25" ID Max. (Rec.), Polyolefin, Thin Wall, Red, Shrink ratio-2:1, 600V, 25 Ft Reel.



By Burndy
Catalog # [HSR12T300PF](#)

Heat Shrink Tubing, 0.50" ID Min.(Exp.), 0.25" ID Max.(Rec.),
Polyolefin, Thin Wall, Red, Shrink ratio-2:1, 600V, 25 Ft Reel.

General

Catalog Number	HSR12T300PF
Color	Red
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810213810

Conductor Related

Conductor Range	#6 AWG to #2 AWG
Conductor Size	6AWG - 2AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSR12T300PF](#)