



HSR14T48PF, Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.12" ID Max. (Rec.), #14 - 10, Polyolefin, Thin Wall, Red, Shrink ratio-2:1, 4 Ft Reel.

By Burndy
Catalog # [HSR14T48PF](#)



Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.12" ID Max.(Rec.),
#14 - 10, Polyolefin, Thin Wall, Red, Shrink ratio-2:1, 4 Ft Reel.

General

Color	Red
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810212554

Conductor Related

Conductor Range	#14 AWG to #10 AWG
Conductor Size	14AWG - 10AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity 1

Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T30OPF_LineArt](#)
- [Sales Drawings - SD211941](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-HSR14T48PF-SPEC-EN | REV 5/2024