



HSR316T300PF, Heat Shrink Tubing, 0.187" ID Min.(Exp.), 0.093" ID Max.(Rec.), #18 - 12, Polyolefin, Thin Wall, Red, Shrink ratio-2:1, 25 Ft Reel.



By Burndy
Catalog # [HSR316T300PF](#)

Heat Shrink Tubing, 0.187" ID Min.(Exp.), 0.093" ID Max.(Rec.), #18 - 12, Polyolefin, Thin Wall, Red, Shrink ratio-2:1, 25 Ft Reel.

General

Color	Red
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810213544

Conductor Related

Conductor Range	#18 AWG to #12 AWG
Conductor Size	18AWG - 12AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity 1

Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
- [Sales Drawings - SD211941](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-HSR316T300PF-SPEC-EN | REV 5/2024