



HSR332T48PF, Heat Shrink Tubing, 0.09" ID Min.(Exp.), 0.04" ID Max. (Rec.), #18 - 16, Polyolefin, Thin Wall, Red, Shrink ratio-2:1, 600V, 4 Ft Reel.

By Burndy
Catalog # [HSR332T48PF](#)



Heat Shrink Tubing, 0.09" ID Min.(Exp.), 0.04" ID Max.(Rec.), #18 - 16, Polyolefin, Thin Wall, Red, Shrink ratio-2:1, 600V, 4 Ft Reel.

General

Color	Red
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810212318

Conductor Related

Conductor Range	#18 AWG to #16 AWG
Conductor Size	18AWG - 16AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Sales Drawings - SD211939-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-HSR332T48PF-SPEC-EN | REV 6/2024