



HSR34FR250, Heat Shrink Tubing, 0.75" ID Min.(Exp.), 0.38" ID Max. (Rec.), #12 - 1/0, PVC, Fire retardant, Thin Wall, Red, 250 Ft Reel.

By Burndy
Catalog # [HSR34FR250](#)



Heat Shrink Tubing, 0.75" ID Min.(Exp.), 0.38" ID Max.(Rec.),
#12 - 1/0, PVC, Fire retardant, Thin Wall, Red, 250 Ft Reel.

General

Color	Red
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810266762

Conductor Related

Conductor Range	#2 AWG to # 1/0 AWG
Conductor Size	1/0AWG - 3/0AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)



A proud member of the Hubbell Family.