



HSR38T1200PF, Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max. (Rec.), #8 - 6, Polyolefin, Thin Wall, Red, Shrink ratio-2:1, 100 Ft Reel.



By Burndy
Catalog # [HSR38T1200PF](#)

Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max.(Rec.), #8 - 6, Polyolefin, Thin Wall, Red, Shrink ratio-2:1, 100 Ft Reel.

General

Catalog Number	HSR38T1200PF
Color	Red
Material	POLYOLEFIN
UPC	781810242605

Conductor Related

Conductor Range	#8 AWG to #6 AWG
-----------------	------------------

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSR38T1200PF](#)