



## HSTPCL02504FPK25EA, Thin Wall Polyolefin Heat Shrink Tubing, Clear, 25-Pack, 4' Lengths, 1/4" ID

By Burndy

Catalog # [HSTPCL02504FPK25EA](#)

1/4 I.D., Qty 25 = 25 Pieces, Color = Clear, 2:1 Ratio, Thin Wall Polyolefin Heat Shrink, 600V Max, Shrink Temp 90°C Min, -55°C To 135°C Continuous Operating Temp., Store At 21°C.

### Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

### General



Catalog Number

HSTPCL02504FPK25EA

Color

Clear

UPC

621945699663

### Product Assets

[Brochures - Polyolefin Thin Wall Heat Shrink Brochure](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Literature - Distributor Promotion: HS-TP Thin Wall Polyolefin Heat Shrink Expires 12-31-2024](#)  
[Sales Drawings - 50139507](#)  
[Specifications - HSTPCL02504FPK25EA](#)