



**HSW12FR, Heat Shrink Tubing,
0.50" ID Min.(Exp.), 0.25" ID Max.
(Rec.), #6 - #4, PVC, Fire retardant,
Thin Wall, White, 50 Ft Reel.**



By Burndy
Catalog # [HSW12FR](#)

Heat Shrink Tubing, 0.50" ID Min.(Exp.), 0.25" ID Max.(Rec.), #6 - #4, PVC, Fire retardant, Thin Wall, White, 50 Ft Reel.

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

General

Catalog Number	HSW12FR
Color	White
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810266885

Conductor Related

Conductor Range	#6 AWG to #4 AWG
Conductor Size	4AWG - 1AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	16
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSW12FR](#)