



## HSW14FR, Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.13" ID Max. (Rec.), #12 - #10, PVC, Fire retardant, Thin Wall, White, 50 Ft Reel.



By Burndy  
Catalog # [HSW14FR](#)

Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.13" ID Max.(Rec.), #12 - #10, PVC, Fire retardant, Thin Wall, White, 50 Ft Reel.

### Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

### General

Catalog Number	HSW14FR
Color	White
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810266908

### Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12AWG -8AWG

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Minimum Pack Quantity	48
-----------------------	----

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSC100FR\\_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSW14FR](#)
- [Video - Heat Shrink Product Overview & Installation](#)