



**HSW14T48PF, Heat Shrink Tubing,
0.25" ID Min.(Exp.), 0.125" ID Max.
(Rec.), #14 - 10, Polyolefin, Thin
Wall, White, Shrink ratio-2:1, 600V,
4 Ft Reel.**



By Burndy
Catalog # [HSW14T48PF](#)

Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.125" ID Max.(Rec.), #14 - 10, Polyolefin, Thin Wall, White, Shrink ratio-2:1, 600V, 4 Ft Reel.

General

Catalog Number	HSW14T48PF
Color	White
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810212592

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	14AWG - 10AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSW14T48PF](#)