



# HSW18FR250, Heat Shrink Tubing, 0.13" ID Min.(Exp.), 0.06" ID Max. (Rec.), #16 - #14, PVC, Fire retardant, Thin Wall, White, 250 Ft Reel.



By Burndy  
Catalog # [HSW18FR250](#)

Heat Shrink Tubing, 0.13" ID Min.(Exp.), 0.06" ID Max.(Rec.),  
#16 - #14, PVC, Fire retardant, Thin Wall, White, 250 Ft Reel.

## General

Color	White
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810266939

## Conductor Related

Conductor Range	#16 AWG to #14 AWG
Conductor Size	16AWG - 14AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	16
-----------------------	----

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSC100FR\\_LineArt](#)
- [Sales Drawings - 50015598](#)



A proud member of the Hubbell Family.