



**HSW38FR, Heat Shrink Tubing,  
0.38" ID Min.(Exp.), 0.19" ID Max.  
(Rec.), #8 - #6, PVC, Fire retardant,  
Thin Wall, White, 50 Ft Reel.**



By Burndy  
Catalog # [HSW38FR](#)

Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max.(Rec.), #8 - #6, PVC, Fire retardant, Thin Wall, White, 50 Ft Reel.

**Features**

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

**General**

Catalog Number	HSW38FR
Color	White
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810266977

**Conductor Related**

Conductor Range	#8 AWG to #6 AWG
Conductor Size	6AWG -4AWG

**Certifications And Compliance**

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

**Logistics**

Minimum Pack Quantity	32
-----------------------	----

**Product Assets**

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSC100FR\\_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSW38FR](#)