



HSY316T300PF, Heat Shrink Tubing, 0.19" ID Min.(Exp.), 0.09" ID Max. (Rec.), #18 - 12, Thin Wall, Yellow, 25 Ft Reel



By Burndy
Catalog # [HSY316T300PF](#)

Heat Shrink Tubing, 0.19" ID Min.(Exp.), 0.09" ID Max.(Rec.), #18 - 12, Polyolefin, Thin Wall, Yellow, Shrink ratio-2:1, 600V, 25 Ft Reel.

General

Catalog Number	HSY316T300PF
Color	Yellow
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810213551

Conductor Related

Conductor Range	#18 AWG to #12 AWG
Conductor Size	18AWG - 12AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSY316T300PF](#)