



HSY38T300PF, Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max. (Rec.), #8 - 6, Polyolefin, Shrink ratio-2:1, Thin Wall, Yellow, 25 Ft Reel.



By Burndy
Catalog # [HSY38T300PF](#)

Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max.(Rec.), #8 - 6, Polyolefin, Shrink ratio-2:1, Thin Wall, Yellow, 25 Ft Reel.

General

Catalog Number	HSY38T300PF
Color	Yellow
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810213698

Conductor Related

Conductor Range	#8 AWG to #6 AWG
Conductor Size	8AWG - 6AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSY38T300PF](#)