

## J1252, Copper Bail, Tin Plated

By Burndy  
Catalog # J1252



Tin plated, hard drawn copper bail designed to make hot-line clamp adapter using HYCRIMP, CABELOK, CRIMPIT or Figure 6-shaped CRIMPIT connectors.

### Application

Designed To Make Hot-Line Clamp Adapter Using HYCRIMP, CABELOK CRIMPIT Or Figure 6 -Shaped CRIMPIT Connectors

### General

Catalog Number	J1252
EU RoHS Indicator	Yes
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	CONNECTOR
Type	Bail
UPC	781810014097
UPC 12 Digit	7818100140977

### Dimensions

Diameter	0.38 in
Dimension - Height inch	4.25 in

### Conductor Related

Conductor - ACSR Str Size	397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee kcmil
Conductor - AL Str Size	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil
Conductor - AL Str Size Range	2/0 AWG-400 kcmil

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	2400

### Product Assets

- [3D Models - J1252\\_MODEL-STEP](#)
- [3D Models - J1252\\_MODEL-PDF](#)
- [3D Models - J1252\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_j990la](#)
- [Sales Drawings - 213076](#)
- [Specifications - J1252](#)