

J990, Copper Bail, Tin Plated

By Burndy
Catalog # J990



Copper Bail for Compression C Connector, Electro Tin Plated.

Application

Designed To Make Hot-Line Clamp Adapter Using HYCRIMP, CABELOK CRIMPIT Or Figure 6 -Shaped CRIMPIT Connectors

General

Catalog Number	J990
EU RoHS Indicator	Yes
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CONNECTOR
Type	Bail
UPC	781810014080
UPC 12 Digit	7818100140800

Dimensions

Diameter	0.25 in
Dimension - Height inch	4.1 in

Conductor Related

Conductor - ACSR Str Size	266.8 (18/1) Waxwing kcmil
Conductor - ACSR Str Size Range	266.8 (18/1) Waxwing kcmil
Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - AL Str Size Range	6 AWG-250 kcmil

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	7200

Product Assets

- [3D Models - J990_MODEL-IGES](#)
- [3D Models - J990_MODEL-STEP](#)
- [3D Models - J990_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_j990la](#)
- [Sales Drawings - SA..053012-01](#)
- [Specifications - J990](#)