



# K11A39U2N, Aluminum Universal Terminal, 2 Hole, Two: 1/0 AWG (Str)-750 kcmil, 3/8" Stud, NEMA Spacing, 2 Screws, Al/Cu Rated, Tin Plated.

By Burndy  
Catalog # K11A39U2N



Aluminum Universal Terminal, 2 Hole, Two: 1/0 AWG (Str)-750 kcmil, 3/8" Stud, NEMA Spacing, 2 Screws, Al/Cu Rated, Tin Plated.

## Features

- AL9CU Dual Rated for both copper an aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing)
- 600 Volt Rated
- Range Taking conductor port

## Application

Terminate multiple conductors onto equipment pads, panel boards, or switchgear

## General

Connector Type	Stacked
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Number of Screws	2
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	621945455986
UPC 12 Digit	6219454559866

## Dimensions

Dimension - Bolt Size fraction	3/8
Dimension - Height fraction	3 in
Dimension - Height inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	144 mm
Dimension - Length Overall inch	5.69 in
Dimension - Screw Size inch	15/16
Dimension - Stud Size fraction	3/8
Dimension - Width inch	1.50 in
Dimension - Width mm	38 mm
Dimensions	5.34 in x 1.50 in x 3.00 in
Height	3 in

## Conductor Related

Conductor - AL Str Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil
Conductor - AL Str Size Range	1/0 AWG-750 kcmil
Conductor - Copper Solid Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	1/0 AWG-4/0 AWG
Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Size Range	1/0 -750 kcmil
Conductor Range	750 Kcmil - #1/0 AWG
Conductor Size	1/0 AWG-750 KCMIL
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> </ul>
Number of Conductors	2

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B

## Logistics

Minimum Pack Quantity	50
-----------------------	----

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50094863](#)

Height	3 in
Length	5.34 in
Thickness	0.5 in
Width	1.5 in

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-K11A39U2N-SPEC-EN | REV 5/2024