



K16P6C5P1/OCAG1, AL Neutral Bar, #14-1/0 AWG, #14-6 AWG, 21 Circuits

By Burndy

Catalog # [K16P6C5P1/OCAG1](#)



Dual rated Aluminum Neutral bar for copper and aluminum conductors, 21 Circuits, 14-1/0 AWG , 14-6AWG wire range.

General

Catalog Number	K16P6C5P1/OCAG1
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810665596
UPC 12 Digit	7818106655966

Dimensions

Dimension - Height inch	0.62 in
Dimension - Height mm	15.7 mm
Dimension - L Length Overall mm	177 mm
Dimension - Length Overall inch	6.97 in
Dimension - Width inch	0.38 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size Range	(4) 14-1/0 AWG , (17) 14-6 AWG
-------------------------------	--------------------------------

Conductor - Copper Str Size Range	(4) 14-1/0 AWG , (17) 14-6 AWG
Number of Conductors	21

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	150
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50038333](#)
- [Specifications - BURNDY_K16P6C5P1OCAG1_Specsheet](#)
- [Specifications - K16P6C5P1/OCAG1](#)