



K2A26U, AL Universal Terminal, 2 Conductor, 1-Hole, #14-2/0 AWG, 1/4" Stud, 2 Screws, Al/Cu Rated

By Burndy
Catalog # K2A26U



Aluminum Universal Terminal, 2 Conductor, 1 Hole, 14-2/0 AWG (Str), 1/4" Stud, 2 Screws, Al/Cu Rated, Tin Plated.

Application

For Aluminum And Copper Conductors

General

| | |
|---------------------------------------|---------------------------|
| Connector Type | Parallel Set-Screw |
| EU RoHS Indicator | No |
| Hardware Type | 3/8 UNC Slotted Set Screw |
| Installation Torque Recommended in-lb | 120 LBS/in |
| Material | Aluminum |
| Material - Hardware | Aluminum |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Screw Type | Slot |
| Plated | N |
| Plating Type | Tin plated |
| Sub Brand | UNIVERSAL TERM |
| Temperature Rating | 194 |
| Type | Bolted Lugs & Terminals |
| UPC | 781810600054 |
| UPC 12 Digit | 7818106000544 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - Bolt Hole Size inch | 0.25 in |
| Dimension - Bolt Size fraction | 1/4 |
| Dimension - D inch | 0.81 in |
| Dimension - Height fraction | 4/5 in |
| Dimension - Height inch | 0.80 in |
| Dimension - Hole Size inch | 0.27 in |
| Dimension - Hole Size mm | 7 mm |
| Dimension - L Length Overall mm | 37 mm |
| Dimension - Length Overall inch | 1.47 in |
| Dimension - N inch | 0.44 in |
| Dimension - Pad Width inch | 1.27 in |
| Dimension - Screw Size inch | 3/8 |
| Dimension - Stud Size inch | 1/4 in |
| Dimension - Width fraction | 1-1/4 in |
| Dimension - Width inch | 1.27 in |
| Dimension - Width mm | 32 mm |

Electrical Ratings

Rating - Minimum Voltage 600

Conductor Related

| | |
|-----------------------------------|---|
| Conductor - AL Str Size | 8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG |
| Conductor - AL Str Size Range | 14 Str-2/0 AWG |
| Conductor - Copper Str Size | 14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG |
| Conductor - Copper Str Size Range | 14 Str-2/0 AWG |
| Conductor Size | 14-2/0 AWG |
| Conductor Type | <ul style="list-style-type: none">AL C Str-SizeCU C Str-Size |
| Number Of Conductors | 2 |

Certifications and Compliance

| | |
|---|--------------|
| Certification - CSA Approved | Yes |
| Certification - UL Listed Direct Burial | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 432 |
| Minimum Pack Quantity | 1 |

Product Assets

[3D Models - K2A26U_MODEL-STEP](#)
[3D Models - K2A26U_MODEL-IGES](#)
[3D Models - K2A26U_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - se210997](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-K2A26U-SPEC-EN | REV 1/2024