



# K2A36U, AL Universal Terminal, 2 Conductor, 1-Hole, #2 AWG Str-600 kcmil, 1/2" Stud, 2 Screws, Al/Cu Rated

By Burndy  
Catalog # [K2A36U](#)



Aluminum Universal Terminal, 2 Conductor, 1 Hole, 2 AWG (Str)-600 kcmil, 1/2" Stud, 2 Screws, Al/Cu Rated, Tin Plated.

## Features

Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

## Application

For Aluminum And Copper Conductors

## General

Connector Type	Parallel Set-Screw
EU RoHS Indicator	Yes
Hardware Type	3/8 UNC Slotted Set Screw
Installation Torque Recommended in-lb	375 LBS/in
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Tin plated
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810600207
UPC 12 Digit	7818106002077

## Dimensions

Dimension - Bolt Hole Size inch	0.50 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	1.75 in
Dimension - Height fraction	1.5714285714285714 in
Dimension - Height inch	1.58 in
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.20 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	2.42 in
Dimension - Screw Size inch	3/8
Dimension - Stud Size inch	1/2 in
Dimension - Width fraction	2-41/100 in

## Conductor Related

Conductor - AL Str Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Size Range	2 Str. - 600 Kcmil
Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil
Conductor - Copper Str Size Range	2 Str. - 600 Kcmil
Conductor Size	2 AWG-600 KCMIL
Conductor Type	<ul style="list-style-type: none"> <li>AL C Str-Size</li> <li>CU C Str-Size</li> </ul>
Number of Conductors	2

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Carton Quantity	72
Minimum Pack Quantity	1

## Product Assets

- [3D Models - K2A36U\\_MODEL-IGES](#)
- [3D Models - K2A36U\\_MODEL-PDF](#)
- [3D Models - K2A36U\\_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR\\_K2AU\\_Lineart](#)
- [Sales Drawings - se210997](#)

Dimension - Width inch 2.42 in  
Dimension - Width mm 61 mm

**Electrical Ratings**

Voltage - Maximum 35000  
Voltage Rating 35000 V



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-K2A36U-SPEC-EN | REV 5/2024