

K2A44U, AL Universal Terminal, 2 Conductor, 1-Hole, 500-1000 kcmil, 5/8" Stud, 2 Screws, Al/Cu Rated

By Burndy
Catalog # K2A44U



Aluminum Universal Terminal, 2 Conductor, 1 Hole, 500-1000 kcmil, 5/8" Stud, 2 Screws, Al/Cu Rated, Tin Plated.

Features

- Constructed from high strength, extruded aluminum alloy
- Electro tin-plated to provide low contact resistance

General

Catalog Number	K2A44U
Connector Type	Parallel Set-Screw
Hardware Type	3/8 UNC Slotted Set Screw
Installation Torque	500 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Tin plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810600306
UPC 12 Digit	7818106003066

Dimensions

Dimension - Bolt Hole Size inch	0.63 in
Dimension - Bolt Size fraction	5/8
Dimension - D inch	1.66 in
Dimension - Height fraction	2 in
Dimension - Height inch	1.95 in
Dimension - Height mm	49.5 mm
Dimension - Hole Size inch	0.66 in
Dimension - Hole Size mm	17 mm
Dimension - L Length Overall mm	89 mm
Dimension - Length Overall inch	3.50 in
Dimension - N inch	0.88 in
Dimension - Pad Width inch	3.52 in
Dimension - Screw Size inch	3/8
Dimension - Stud Size inch	5/8 in
Dimension - Width fraction	3-13/25 in
Dimension - Width inch	3.52 in
Dimension - Width mm	89 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil;1000 kcmil
Conductor - AL Str Size Range	500 -1000 Kcmil
Conductor - Copper Str Size	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Size Range	500 -1000 Kcmil
Conductor Size	500-1000 KCMIL
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size
Number of Conductors	2

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
Pallet Quantity	36

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_K2AU_Lineart](#)
[Sales Drawings - se210997](#)
[Specifications - K2A44U](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-K2A44U-SPEC-EN | REV 10/2024