



K2C26TN, SERVIT POST Mechanical Connector, 2 Cables to Flat

By Burndy
Catalog # [K2C26TN](#)



Tin plated; Accepts 2 conductors; #2 - 2/0 Stranded Copper; #2 - 3/0 Solid Copper; 1/2" Stud.

General

Catalog Number	K2C26TN
Material	Bronze Alloy, Leaded
Plated	Y
Plating Type	Tin Plated
Stud Installation Torque inch pounds	480 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810258361
UPC 12 Digit	7818102583611

Dimensions

Dimension - B Length inch	0.52 in
Dimension - Body Width inch	0.88 in
Dimension - D inch	0.75 in
Dimension - Height inch	1.81 in
Dimension - L Length Overall mm	64 mm
Dimension - Length Overall inch	2.53 in
Dimension - Nut Width inch	1.04 in
Dimension - P inch	0.44 in

Conductor Related

Conductor - Copper Solid Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - Copper Solid Size Range	2 AWG-3/0 AWG
Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	2 AWG-2/0 AWG
Physical Attribute - Number of Conductors Accommodated Total	2

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	5800

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_K2C_Lineart](#)
[Sales Drawings - 10020944](#)
[Specifications - K2C26TN](#)