



K2C28TN, SERVIT POST Mechanical Connector, 2 Cables to Flat

By Burndy
Catalog # [K2C28TN](#)



Tin plated; Accepts 2 conductors; #1 Stranded Copper - 4/0 Solid Copper; 5/8" Stud.

General

Material	Bronze Alloy, Leaded
Plated	Y
Plating Type	Tin Plated
Stud Installation Torque inch pounds	660 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810215982
UPC 12 Digit	7818102159822

Dimensions

Dimension - B Length inch	0.75 in
Dimension - Body Width inch	1.18 in
Dimension - D inch	1.00 in
Dimension - Height inch	2.46 in
Dimension - L Length Overall mm	87 mm
Dimension - Length Overall inch	3.44 in
Dimension - Nut Width inch	1.35 in
Dimension - P inch	0.55 in

Conductor Related

Conductor - Copper Solid Size	1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	1 AWG-4/0 AWG
Conductor - Copper Str Size	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	1 AWG-4/0 AWG
Physical Attribute - Number of Conductors Accommodated Total	2

Certifications And Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_K2C_Lineart](#)
[Sales Drawings - 10020944](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-K2C28TN-SPEC-EN | REV 5/2024