



K2P4CAG1, AL Neutral Bar, Dual Rated, 2 Circuits, #14-4 AWG Wire Range

By Burndy
Catalog # [K2P4CAG1](#)



Dual rated Aluminum Neutral bar for copper and aluminum conductors, 2 Circuits, 14-4 AWG wire range.

General

Catalog Number	K2P4CAG1
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810665527
UPC 12 Digit	7818106655277

Dimensions

Dimension - Height inch	0.44 in
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.09 in
Dimension - Width inch	0.31 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size Range	14-4 AWG
Conductor - Copper Str Size Range	14-4 AWG
Number of Conductors	2

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	150
Minimum Pack Quantity	1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50038325](#)
[Specifications - K2P4CAG1](#)