



# K3A27U2N, AL Universal Terminal, 3 Conductor, #6-3/0 AWG Str, 1/2" Stud, 1.75" Spacing, 3 Screws, Al/Cu Rated

By Burndy  
Catalog # [K3A27U2N](#)



Aluminum Universal Terminal, 3 Conductor, 2 Hole, 6-3/0 AWG (Str), 1/2" Stud, 1.75" Stud Hole Spacing, 3 Screws, Al/Cu Rated, Tin Plated.

## Features

Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

## Application

For Aluminum and Copper Conductors

## General

Connector Type	Parallel Set-Screw
EU RoHS Indicator	No
Installation Torque Recommended in-lb	275 LBS/in
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	3
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin plated
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810370391
UPC 12 Digit	7818103703911

## Dimensions

Dimension - Bolt Hole Size inch	0.57 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.00 in
Dimension - Height fraction	1.125 in
Dimension - Height inch	1.12 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	108 mm
Dimension - Length Overall inch	4.25 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	2.83 in
Dimension - Stud Size inch	1/2 in

## Conductor Related

Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - AL Str Size Range	6 Str.-3/0 AWG
Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG
Conductor - Copper Str Size Range	6 Str.-3/0 AWG
Conductor Size	6-3/0 AWG
Conductor Type	<ul style="list-style-type: none"><li>AL C Str-Size</li><li>CU C Str-Size</li></ul>
Number of Conductors	3

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
UL Listed	Yes

## Logistics

Carton Quantity	60
Minimum Pack Quantity	1

## Product Assets

[3D Models - K3A27U2N\\_MODEL-PDF](#)  
[3D Models - K3A27U2N\\_MODEL-IGES](#)  
[3D Models - K3A27U2N\\_MODEL-STEP](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_K3AU\\_LineArt](#)  
[Sales Drawings - se210997](#)

Dimension - Standard inch	1.72 in
Dimension - Width fraction	2-81/100 in
Dimension - Width inch	2.83 in
Dimension - Width mm	71 mm

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-K3A27U2N-SPEC-EN | REV 5/2024