



## K3A27U4N, AL Universal Terminal, 3 Conductor, #6-3/0 AWG Str, 1/2" Stud, 1.75" Spacing, 3 Screws, Al/Cu Rated

By Burndy

Catalog # [K3A27U4N](#)



Aluminum Universal Terminal, 3 Conductor, 4 Hole, 6-3/0 AWG (Str), 1/2" Stud, 1.75" Stud Hole Spacing, 3 Screws, Al/Cu Rated, Tin Plated.

### Features

- Constructed from high strength aluminum alloy
- Electro tin plating proving low contact resistance

### General

Catalog Number	K3A27U4N
Connector Type	Parallel Set-Screw
Installation Torque	275 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Number of Screws	3
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810370414
UPC 12 Digit	7818103704144

### Dimensions

Dimension - Bolt Hole Size inch	0.57 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.00 in
Dimension - Height fraction	1.125 in
Dimension - Height inch	1.12 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	108 mm
Dimension - Length Overall inch	4.25 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	2.83 in
Dimension - Stud Size inch	1/2 in
Dimension - Width fraction	2-81/100 in
Dimension - Width inch	2.83 in
Dimension - Width mm	71 mm

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - AL Str Size Range	6 Str.-3/0 AWG
Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG
Conductor - Copper Str Size Range	6 Str.-3/0 AWG
Conductor Size	6-3/0 AWG
Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Size</li><li>• CU C Str-Size</li></ul>
Number of Conductors	3

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
Pallet Quantity	60

## Product Assets

[3D Models - K3A27U4N\\_MODEL-IGES](#)  
[3D Models - K3A27U4N\\_MODEL-STEP](#)  
[3D Models - K3A27U4N\\_MODEL-PDF](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_K3AU\\_LineArt](#)  
[Sales Drawings - se210997](#)  
[Specifications - K3A27U4N](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-K3A27U4N-SPEC-EN | REV 8/2024