

# K6B28262N, Cu, Multiple Outlet Transformer Term, Lg Groove: #6-4/0 AWG, Sm Groove: #6 Str-2/0 AWG, 2-Hole, 1/2" Stud, 1.75" Spacing



By Burndy  
Catalog # [K6B28262N](#)

Cast Cu Alloy URD Multiple Transformer Terminal, 2-NEMA Holes, #6 - 4/0 AWG (Large Groove) #6 Str - 2/0 AWG (Small Groove), 9/16" Hole Dia.

## General

Catalog Number	K6B28262N
Connector Type	Terminal
Material	Copper
Material - Hardware	Brass
Physical Attribute - Number of Holes	2
Plating Type	Unplated
Trade Name	KA-LUG™
UPC	781810189108
UPC 12 Digit	7818101891088

## Dimensions

Dimension - D inch	3.19 in
Dimension - Hole Size fraction	14/25
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	7.75 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.15 in

## Conductor Related

Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0
-----------------------------	--

Conductor - Copper Str Size Range	AWG;3/0 AWG;4/0 AWG 6 AWG-4/0 AWG
-----------------------------------	--------------------------------------

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_K6B\\_URD\\_TRANSFORMER\\_FIG1\\_LineArt](#)
- [Sales Drawings - 50860](#)
- [Specifications - K6B28262N](#)