



K6B284N, Cu, Underground Multiple Outlet Transformer Term, #6-4/0 Str AWG, 4-Holes, 1/2" Stud, 1.75" Spacing, 6 Outlets



By Burndy
Catalog # [K6B284N](#)

Cast Cu Alloy URD Transformer Terminals(NEMA Tongue), 4 Holes, #6 - 4/0 Str AWG Cu Cable (6 Outlets).

General

Catalog Number	K6B284N
Connector Type	Terminal
Material	Copper Alloy
Material - Hardware	Brass
Physical Attribute - Number of Holes	4
Plating Type	Unplated
Trade Name	KA-LUG™
UPC	781810189153
UPC 12 Digit	7818101891533

Dimensions

Dimension - D inch	3.19 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size fraction	14/25
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	8.12 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	3 in

Conductor Related

Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	6 AWG-4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_K6B_URD_TRANSFORMER_FIG2_LineArt](#)
- [Sales Drawings - SC051033-01](#)
- [Specifications - K6B284N](#)