



K6P28TN, Cu, Underground Multiple Outlet Transformer Terminal, #6-4/0 Str, supplied with cover

By Burndy
Catalog # [K6P28TN](#)



Tin plated, Copper alloy connector for use on copper conductors #6 - 4/0 Stranded; Supplied with insulating cover.

General

Catalog Number	K6P28TN
Connector Type	Multiple Service Connector
Material	Copper Alloy
Material - Hardware	Brass
Number Of Outlets	6
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810089828
UPC 12 Digit	7818100898288

Dimensions

Dimension - B Length fraction	2-3/4 in
Dimension - B Length inch	2.75 in
Dimension - Pad Width inch	1.63 in

Conductor Related

Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	6 AWG-4/0 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - K6P28TN](#)