

KA252TC38H, Cu Mounting Set Screw Lug, 2-Hole, 1/0-4/0 Str, 3/8" Stud

By Burndy
Catalog # [KA252TC38H](#)



Mechanical Terminal for Copper; Accommodates: 1/0 - 4/0 Str;
Stud: 3/8"; 2-Hole Pad; Installation Torque: 275 in-lbs.

Features

- Dual-rated Universal Terminal constructed from high strength aluminum alloy and electro tin-plated to provide low contact resistance

General

Catalog Number	KA252TC38H
Connector Type	Terminal
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Screw Type	Allen
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810536223

Dimensions

Dimension - Height inch	0.94 in
Dimension - Height mm	0 mm
Dimension - Hole Size inch	0.42 in
Dimension - Length Overall inch	2.69 in
Dimension - N inch	0.38 in
Dimension - Pad Width inch	0.94 in

Conductor Related

Conductor - Copper Str Size	# 1Str. - 4/0 Str.
Conductor Type	CU C Str-Size
Number Of Wires	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sc074265-01](#)
[Specifications - KA252TC38H](#)