

KA25UG4, AL Set Screw Terminal, #14-1/0 Str, Dual Rated

By Burndy
Catalog # KA25UG4



Universal Terminal, #14 - 1/0 Stranded; Dual Rated.

Features

Dual rated panelboard lugs constructed from high strength extruded aluminum alloy, electro tin-plated to provide low contact resistance

General

Catalog Number	KA25UG4
Hardware Type	7/16 Hex/Socket SetScrew
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810363416

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - D inch	3.25 in
Dimension - Height fraction	1-9/50 in
Dimension - Height inch	1.19 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	108 mm
Dimension - Length Overall inch	4.25 in
Dimension - N inch	0.63 in

Dimension - Pad Width inch 1.00 in

Conductor Related

Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size Range	6 AWG-2/0 AWG
Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	6 AWG-2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • AL C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	500
Pallet Quantity	72

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50018770](#)
[Specifications - KA25UG4](#)