



KA26U2G1, AL Set Screw Terminal, #14-2/0 Str, Dual Rated

By Burndy
Catalog # KA26U2G1

#14 - 2/0 Stranded; Dia; Rated.



Features

Dual rated panelboard lugs constructed from high strength extruded aluminum alloy, electro tin-plated to provide low contact resistance

General

Catalog Number	KA26U2G1
Connector Type	Terminal
Material	Aluminum
Number Of Ports	1
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810653968
UPC 12 Digit	7818106539688

Dimensions

Dimension - Height inch	0.88
Dimension - Hole Size inch	0.27
Dimension - Length Overall inch	2.06
Dimension - N inch	0.31

Dimension - Width inch 0.63

Electrical Ratings

Rating - Minimum Voltage 600

Conductor Related

Conductor - AL Str Size Range	#14 AWG to 2/0 kcmil
Conductor - Copper Str Size Range	#14 AWG to 2/0 kcmil
Conductor Type	<ul style="list-style-type: none">AL C Str-SizeCU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - KA26U2G1](#)