

# KA28G13HEXUNPL, Cu Set Screw Lug, #1-4/0 Str, Cu, 1/2" Stud, Unplated



By Burndy  
Catalog # KA28G13HEXUNPL

#1 - 4/0 Stranded Copper; 1/2" stud; unplated.

## General

Catalog Number	KA28G13HEXUNPL
Connector Type	Terminal
Hardware Type	5/8 UNF HexScrew
Material	Copper
Material - Hardware	Stainless Steel
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810227541
UPC 12 Digit	7818102275411

## Dimensions

Dimension - B Length fraction	64/79 in
Dimension - B Length inch	0.81 in
Dimension - Height fraction	1.02 in
Dimension - Height inch	1.02 in
Dimension - Height mm	25.9 mm
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94 in
Dimension - N inch	0.44 in

Dimension - Pad Width inch 0.94 in

## Electrical Ratings

Rating - Minimum Voltage 600

## Conductor Related

Conductor - Copper Str Size 1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG

Conductor - Copper Str Size Range 1 AWG-4/0 AWG

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity 1

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - KA28G13HEXUNPL](#)