

KA28H, Cu Set Screw Terminal, #1-4/0 Str, 3/8" Stud

By Burndy
Catalog # KA28H



Mechanical Terminal for Copper; Accommodates: #1 - 4/0 Str; Stud: 3/8"; Installation Torque: 275 in-lbs.

General

Catalog Number	KA28H
Connector Type	Terminal
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Screw Type	Allen
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810528402

Dimensions

Dimension - B Length inch	0.81 in
Dimension - Height inch	1.25 in
Dimension - Hole Size inch	0.42 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94 in
Dimension - N inch	0.44 in
Dimension - Pad Width inch	0.94 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Size Range	# 1Str. - 4/0 Str.
Number Of Wires	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

- [3D Models - KA28H_MODEL-IGES](#)
- [3D Models - KA28H_MODEL-STEP](#)
- [3D Models - KA28H_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50026771](#)
- [Specifications - KA28H](#)