

KA29UG12, AL Set Screw Connector, #2 Str-250 kcmil, 3/8" Stud

By Burndy
Catalog # [KA29UG12](#)



Universal Terminal, #2 Stranded - 250 kcmil; 3/8" stud.

Features

- Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

General

Catalog Number	KA29UG12
Material	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810495087

Dimensions

Dimension - D inch	.94 in
Dimension - Height inch	1.14 in
Dimension - Height mm	0 mm
Dimension - Hole Size inch	0.42 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.00 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size Range	6 Str. - 250 Kcmil
Conductor - Copper Str Size Range	6 Str. - 250 Kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • AL C Str-Size
Number Of Wires	1

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	500
-----------------------	-----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - se210997](#)
- [Specifications - KA29UG12](#)