



KA2UG7, AL Set Screw Connector, #14-2 Str Al/Cu, AL9CU, 1/4" Stud

By Burndy
Catalog # [KA2UG7](#)

Universal Terminal, #14 - 2 Stranded Aluminum/Copper;
AL9CU; hex head screw 1/4"; Recommended torque 50 lb-in.



Features

Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

General

Material	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin Plated
Type	Bolted Lugs & Terminals
UPC	781810541098

Dimensions

Dimension - Height inch	0.55 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.16 in

Conductor Related

Conductor - AL Str Size Range	2 Str. - 14 Str.
Conductor - Copper Str Size	2 Str. - 14 Str.
Conductor Type	CU C Str-Size
Number Of Wires	1

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1800
Minimum Pack Quantity	10000

Product Assets

[3D Models - KA2UG7_MODEL-PDF](#)
[3D Models - KA2UG7_MODEL-IGES](#)
[3D Models - KA2UG7_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 30023850](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-KA2UG7-SPEC-EN | REV 5/2024