



KA34H, Mechanical Terminal for Copper; Accommodates: 4/0 AWG Str - 500 kcmil; Stud: 1/2"; Installation Torque: 375 in-lbs

By Burndy
Catalog # [KA34H](#)



Mechanical Terminal for Copper; Accommodates: 4/0 AWG Str - 500 kcmil; Stud: 1/2"; Installation Torque: 375 in-lbs.

General

Connector Type	Terminal
Material	Copper
Plated	N
Plating Type	Unplated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810536230

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	18
-----------------------	----

Product Assets

- [3D Models - KA34H_MODEL-STEP](#)
- [3D Models - KA34H_MODEL-IGES](#)
- [3D Models - KA34H_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Sales Drawings - 50026771](#)



A proud member of the Hubbell Family.