

# KA8CH, #14 Solid - #8 Stranded Copper; #10 Stud; 45 in-lb recommended torque



By Burndy  
Catalog # [KA8CH](#)

#14 Solid - #8 Stranded Copper; #10 Stud; 45 in-lb recommended torque.

## General

Catalog Number	KA8CH
Connector Type	Terminal
Material	Copper
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	KA-LUG™
Type	Bolted Lugs & Terminals
UPC	781810528358
UPC 12 Digit	7818105283588

## Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

## Certifications And Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	UI
Status	
UL Listed	No

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

## Product Assets

- [3D Models - KA8CH\\_MODEL-STEP](#)
- [3D Models - KA8CH\\_MODEL-PDF](#)
- [3D Models - KA8CH\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - KA8CH](#)