



## KAP350, 350 kcmil pin adaptor, Torque: 100 N lb, Voltage: 600 V.

By Burndy  
Catalog # [KAP350](#)

350 kcmil pin adaptor, Torque: 100 N lb, Voltage: 600 V.



### Application

Terminate "upsized" conductor and/or fine strand conductor into mechanical connectors found in molded case circuit breakers, panel board equipment, and other switchgear.

### General

Catalog Number	KAP350
Connector Type	Center Formed Adapter
EU RoHS Indicator	Contact Manufacturer
Hex Key	3/8 in
Installation Torque	450
Recommended in-lb	
Material	Aluminum
Sub Brand	Pin Adaptor
Type	1/0 - 350 Mechanical Pin Adaptor; Centered Pin
UPC	621945493339

### Dimensions

Dimension - Strip Length inch	1.11 in
Dimensions	2.75 in x 1.50 in x 2.00 in
Height	2 in
Length	2.75 in
Outside Diameter	1.38 in
Width	1.5 in

### Electrical Ratings

Amperage Rating	350 A
-----------------	-------

### Conductor Related

Conductor - AL Str Size Range	1/0 AWG - 350 kcmil
Conductor - Copper DLO Size Range	1/0 AWG - 350 kcmil
Conductor - Copper Flex H Size Range	1/0 AWG - 350 kcmil
Conductor - Copper Flex I Size Range	1/0 AWG - 350 kcmil
Conductor - Copper Flex K Size Range	1/0 AWG - 350 kcmil
Conductor - Copper Str Size Range	1/0 AWG - 350 kcmil
Conductor Size	1/0 AWG- 350 KCMIL

### Certifications And Compliance

Buy American Compliant	No
------------------------	----

### Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	2250

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50076514](#)  
[Specifications - KAP350](#)