



# KAPO350, 350 Kcmil pin adaptor, Torque: 500 N lb, Voltage: 600 V.

By Burndy  
Catalog # [KAPO350](#)

350 Kcmil pin adaptor, Torque: 500 N lb, Voltage: 600 V.



## Features

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- Rated for use with Fine Strand Conductor
- 600 Volt Rated
- Range Taking conductor port
- Plastisol insulated covers provided with each connector

## Application

Terminate "upsized" conductor and/or fine strand conductor into mechanical connectors found in molded case circuit breakers, panel board equipment, and other switchgear.

## General

|                                       |  |
|---------------------------------------|--|
| Connector Type                        | Offset   |
| EU RoHS Indicator                     | Contact Manufacturer                               |
| Hex Key                               | 3/8 in   |
| Installation Torque Recommended in-lb | 450  |
| Material                              | Aluminum   |
| Sub Brand                             | Pin Adaptor  |
| Type                                  | 1/0 - 350 Mechanical Pin Adaptor; Off-Centered Pin |
| UPC                                   | 621945493360                                       |

## Dimensions

|                               |                             |
|-------------------------------|-----------------------------|
| Dimension - Strip Length inch | 1.11 in                     |
| Dimensions                    | 2.75 in x 1.50 in x 2.00 in |
| Height                        | 2.00 in                     |
| Length                        | 2.75 in                     |
| Outside Diameter              | 1.38 in                     |
| Width                         | 1.50 in                     |

## Electrical Ratings

|                 |       |
|-----------------|-------|
| Amperage Rating | 350 A |
|-----------------|-------|

## Conductor Related

|                                      |                     |
|--------------------------------------|---------------------|
| Conductor - AL Str Size Range        | 1/0 AWG - 350 kcmil |
| Conductor - Copper DLO Size Range    | 1/0 AWG - 350 kcmil |
| Conductor - Copper Flex H Size Range | 1/0 AWG - 350 kcmil |
| Conductor - Copper Flex I Size Range | #6 - 1/0 AWG        |
| Conductor - Copper Flex K Size Range | 1/0 AWG - 350 kcmil |
| Conductor - Copper Str Size Range    | 1/0 AWG - 350 kcmil |
| Conductor Size                       | 1/0 AWG- 350 KCMIL  |

## Logistics

|                       |      |
|-----------------------|------|
| Carton Quantity       | 25   |
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 2250 |

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50076514](#)



A proud member of the Hubbell Family.