



KAPO500R, Wire range: 4/0 -500 kcmil, Torque: 400-600 N lb.

By Burndy
Catalog # [KAPO500R](#)

Wire range: 4/0 -500 kcmil, Torque: 400-600 N lb.



Application

Terminate "upsized" conductor and/or fine strand conductor into mechanical connectors found in molded case circuit breakers, panel board equipment, and other switchgear.

General

Catalog Number	KAPO500R
Connector Type	Offset
Material	Aluminum
Type	<ul style="list-style-type: none">4/0 -500 kcmil Mechanical Pin AdaptorOff-Centered Pin
UPC	621945554177

Dimensions

Dimensions	2.92 in x 1.68 in x 2.43 in
Height	2.43 in
Length	2.92 in
Outside Diameter	1.5
Width	1.68 in

Electrical Ratings

Amperage Rating	430
Voltage Rating	600 V

Conductor Related

Conductor - AL Str Size Range	4/0 AWG -500 kcmil
Conductor - Copper DLO Size Range	4/0 -500 kcmil
Conductor - Copper Flex H Size Range	4/0 -500 kcmil
Conductor - Copper Flex I Size Range	4/0 -500 kcmil
Conductor - Copper Flex K Size Range	4/0 -500 kcmil
Conductor - Copper Str Run	4/0 -500 kcmil
Conductor - Copper Str Size Range	4/0 AWG -500 kcmil
Conductor Size	4/0 AWG-500 KCMIL

Logistics

Carton Quantity	25
Pallet Quantity	2250

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - KAPO500R](#)