



KASB45U12, QIKSHEAR™ Shear Bolt Lug, 1250 kcmil 1-hole

By Burndy
Catalog # [KASB45U12](#)

QIKSHEAR™ Shear Bolt Lug, 1250 kcmil 1-hole, 1/2 hole, 3/8 socket



Features

- No Tooling or Die Investment Required, no crimp tools necessary
- Dual Rated AL9CU for use with both copper and aluminum conductor
- cULus Listed Wire Connector to UL486A-486B
- Up to 35kV voltage rating
- Tin Plated aluminum connectors and bolts reduce galvanic corrosion and oxide build up
- Range-taking capabilities on most sizes

General

Type	Bolted Lugs & Terminals
UPC	621945658882

Dimensions

Length	5.20 in
--------	---------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Installation Manuals - Shear Bolt Mechanical Connector](#)
[Installation Instructions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-KASB45U12-SPEC-EN | REV 1/2024