



KC15, SERVIT POST Mechanical Connector, Cable to Flat

By Burndy
Catalog # [KC15](#)



Mechanical Grounding Connector, Cable to Flat, 12 - 9 AWG (Str) / 12 - 8 AWG (Sol).

Application

For Used To Ground One Or Two Copper Cables To Steel Structures, Fence Posts, Transformers, Tap One Or Two Cables From Bus Bar And Direct Burial

General

| | |
|--------------------------------------|----------------------------|
| EU RoHS Indicator | Yes |
| Material | Bronze, Leaded, Commercial |
| Plated | N |
| Plating Type | Leaded Bronze Alloy |
| Stud Installation Torque inch pounds | 80 LBS/in |
| Sub Brand | SERVIT POST |
| Trade Name | SERVIT POST™ |
| Type | KC and K2C Series |
| UPC | 781810254004 |
| UPC 12 Digit | 7818102540044 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length fraction | 3/8 in |
| Dimension - B Length inch | 0.37 in |
| Dimension - Body Width inch | 0.38 in |
| Dimension - Bolt Size fraction | 1/4 |
| Dimension - D inch | 0.50 in |
| Dimension - Height fraction | 5/8 |
| Dimension - Height inch | 0.69 in |
| Dimension - L Length Overall mm | 30.2 mm |
| Dimension - Length Overall inch | 1.19 in |
| Dimension - Nut Width inch | 0.50 in |
| Dimension - P inch | 0.14 in |
| Dimension - Threads per inch | 20 |
| Dimension - Width inch | 18 mm |

Conductor Related

| | |
|--|----------------------------------|
| Conductor - Copper Solid Size | 12 AWG;11 AWG;10 AWG;9 AWG;8 AWG |
| Conductor - Copper Solid Size Range | 12 AWG-8 AWG |
| Conductor - Copper Str Size | 12 AWG;10 AWG;9 AWG |
| Conductor - Copper Str Size Range | 12 AWG-9 AWG |
| Physical Attribute - Number of Conductors Accommodated Total | 1 |

Certifications and Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 50 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 44550 |

Product Assets

[3D Models - KC15_MODEL-IGES](#)
[3D Models - KC15_MODEL-PDF](#)
[3D Models - KC15_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..055917](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-KC15-SPEC-EN | REV 1/2024

