



# KC17NSP, SERVIT POST Mechanical Connector, Cable to Flat

By Burndy  
Catalog # [KC17NSP](#)



Mechanical Connector; Cable to Flat; Accommodates: #10 - #7 AWG Stranded or #10 - #6 AWG Solid Copper; 1/4" Stud, supplied with split lockwasher and nut; Direct Burial, UL Listed, CSA Certified.

### Features

- SERVIT POST tin-plated mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

### General

Catalog Number	KC17NSP
Material	Bronze, Leaded, Commercial
Plated	N
Plating Type	Unplated
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810467695
UPC 14 Digit GTIN	00781810467695

### Dimensions

Dimension - Height mm	0 mm
-----------------------	------

### Conductor Related

Conductor - Copper Solid Size Range	10 AWG-6 AWG
Conductor - Copper Str Size Range	10 AWG-7 AWG
Physical Attribute - Number of Conductors Accommodated Total	1

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	29700

### Product Assets

- [3D Models - KC17NSP\\_MODEL-STEP](#)
- [3D Models - KC17NSP\\_MODEL-IGES](#)
- [3D Models - KC17NSP\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - KC17NSP](#)



A Hubbell brand